

Inspection & Measurement

Stereo Microscopes

Detailed product specifications are available on: us.100y.com.tw



Part No.	Product No.	Description	Magnificat	Working Dis. (mm)	Eye./Obj.Magnificat	Yes/No Illuminator	Vin	Illuminator power V
40691	IMHM-XTL2B	XTL Series Zoom Stereo Microscope	7X~42X	90mm	10X/0.7X~4.2X	Have exposure / projection lights	110V	110V



Part No.	Product No.	Manufacturer	Description	Magnificat	Eye./Obj.Magnificat	Vin	Illuminator power V	Observation
23748	SMZ140	Motic	SMZ140 Stereo Microscope	10~40X	10X/1~4X	6W Ringlike Lamp	110V/60Hz	TRINOCULAR



Technical Performance:

1. Sharp stereo erect image over a wide field view
2. Upright binocular view head, the interpupillar distance is between 55-75mm
3. The working distance of 2x magnification of objective 70mm
4. Built-in incident light 3V3W
5. Power 2 units of aa batteries
6. Plastic body & easy to carry
7. Each set packed in Styrofoam and in an inner box. Ten sets in one carton

Part No.	Product No.	Manufacturer	Description	Magnificat	Working Dis. (mm)	Eye./Obj.Magnificat	Yes/No Illuminator	Vin	Illuminator power V
17995	STX	NBHG	STX Series stereo microscopes	20X	70mm	10X/2X	Cast	3V/3W	N Battery *2



Technical Performance:

1. Sharp stereo erect image over a wide field view
2. 45° inclined and 360° rotational binocular head with locked-ineyepiece. The left ocular-tube with diopter adjustment ± 5 dp, The interpupillary distance is between 55-75mm
3. Three kinds of 90° rotational objective selection: 1x/2x, 1x/3x, 2x/4x.
4. ZTX-20 series supplied with pillar style stand.
5. Electric apparatus has CE approval
6. Power supply 110V/60Hz or 200V/50Hz
7. Each set packed in styrofoam and in an inner box. Three sets in one carton
8. A wide range of optional accessories.

Part No.	Product No.	Manufacturer	Description	Magnificat	Working Dis. (mm)	Eye./Obj.Magnificat	Yes/No Illuminator	Vin	Illuminator power V	Observation
17997	ZTX-20-W-WF20X-110V	NBHG	ZTX-20 Series stereo microscopes	40X/80X	80mm	20X/2x-4x	Illuminate/Cast	Illuminate:12V/10W Cast:12V/10W	110V/60Hz	BINOCULAR



Technical Performance:

1. Sharp stereo erect image over a wide field view
2. 45° inclined and 360° rotational binocular head with locked-ineyepiece. The left ocular-tube with diopter adjustment ± 5 dp, The interpupillary distance is between 55-75mm.
3. Zoom objective 1x-4x
4. ZTX-E series supplied with pillar style stand, ZTX-E-W series supplied with arm curved style stand ZTX-3E series trinocular
5. Electric apparatus has CE approval
6. Power supply 110V/60Hz or 200V/50Hz
7. Each set packed in styrofoam and in an inner box. Three sets in one carton
8. A wide range of optional accessories.

Part No.	Product No.	Manufacturer	Description	Magnificat	Working Dis. (mm)	Eye./Obj.Magnificat	Yes/No Illuminator	Vin	Illuminator power V	Observation
17996	ZTX-E-SWF20X-110V	NBHG	ZTX-E Series zoom stereo microscopes	10~40X	85mm	10X/1X~4X	Have exposure / projection lights	Irradiation:12V/10W projection:12V/10W	110V/60Hz	BINOCULAR

- We provide a wide range of products to development and maintenance engineers in all type of business
- If you cannot find the components you want on the catalogue, please call us.



Taiwan: 886-3-5753170

Shanghai: 021-54151736 Shenzhen: 0755-83298787

Centenary Materials

Waiting for your phone call



T E L : Taiwan: 886-3-5753170
F A X : Taiwan: 886-3-5753172
E-mail: Taiwan: us_sale@100y.com.tw

Shenzhen: 86-755-83298787
Shenzhen: 86-755-83640655
Shenzhen: 100y@163.com

Shanghai: 86-21-54151736
Shanghai: 86-21-64605107
Shanghai: 100y-1@163.com